

M12 male 90° A-cod. Push-Lock5-pol., 0,14 - 0,75mm², 4 - 8mm

Male 90°

M12, 5-pole



A-coded

Push-Lock spring clamp connection

Sealing range (cable Ø): 4...8 mm

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Product may differ from Image

**Side 1**

Tightening torque	0,4 Nm
Mounting method	inserted, screwed
Family construction form	M12

Thread	M12 x 1
Coding	A
Material contact	Bronze
No. of poles	5
Degree of protection (EN IEC 60529)	IP65, IP67
取引条件	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ETIM-5.0	EC002635
GTIN	4065909028933
HSコード	85366990
Packaging unit	1
Electrical data Supply	
Operating voltage AC	48 V
Operating voltage DC	60 V
Operating voltage AC max. (UL-listed)	250 V
Current operating per contact (UL)	4 A
Operating current per contact max. (40°C)	4 A
Diagnostics	
Status indication LED	no
Installation	
Cross section connection with wire end ferrule min.	0,08 mm²
Cross section connection with wire end ferrule max.	0,5 mm²
Cross section connection without wire end ferrule min.	0,14 mm²
Cross section connection without wire end ferrule max.	0,75 mm²
Cross section connection with wire end ferrule AWG min.	28 AWG
Cross section connection with wire end ferrule AWG max.	20 AWG
Cross section connection without wire end ferrule AWG min.	26 AWG
Cross section connection without wire end ferrule AWG max.	18 AWG
Installation Connection	
Connection information	Push-Lock spring clamp connection
Width across flats	SW18
Mating cycles min.	100
Installation Pin assignment	
Coding	A
Device protection Electrical	
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Insulation resistance min.	100 MΩ
Overvoltage category (EN 60950-1)	II
Mechanical data Material data	
Coating contact	gold plated
Material gasket	NBR

Material housing	PA
Mechanical data Mounting data	
Mounting method	inserted, screwed, Shaking protection
Clamping range min.	4 mm
Clamping range max.	8 mm
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	85 °C
Important installation notes	
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Conformity	
Product standard	DIN EN 61076-2-101 (M12)