

### M12 female 0° B-cod. with cable shielded

PUR 1x2xAWG24 shielded vt UL/CSA+drag ch. 1m

PROFIBUS

Female straight

M12, 2-pole

B-coded

shielded



Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

### [Link to Product](#)

#### Illustration



Product may differ from Image



Cable length

1 m

Side 1

|                                     |                   |
|-------------------------------------|-------------------|
| Tightening torque                   | 0,6 Nm            |
| Mounting method                     | inserted, screwed |
| Family construction form            | M12               |
| Thread                              | M12 x 1           |
| Coding                              | B                 |
| Material                            | PUR               |
| Width across flats                  | SW13              |
| Degree of protection (EN IEC 60529) | IP65, IP66K, IP67 |

Side 2

|                           |       |
|---------------------------|-------|
| Stripping length (jacket) | 20 mm |
|---------------------------|-------|

取引条件

|                |               |
|----------------|---------------|
| ECLASS-6.0     | 27061801      |
| ECLASS-6.1     | 27060307      |
| ECLASS-7.0     | 27060307      |
| ECLASS-8.0     | 27060307      |
| ECLASS-9.0     | 27060307      |
| ECLASS-10.1    | 27060307      |
| ECLASS-11.1    | 27060307      |
| ECLASS-12.0    | 27060307      |
| ETIM-5.0       | EC001855      |
| GTIN           | 4048879375740 |
| HSコード          | 85444290      |
| Packaging unit | 1             |

Electrical data | Supply

|                                    |      |
|------------------------------------|------|
| Operating voltage AC max.          | 60 V |
| Operating voltage DC max.          | 60 V |
| Operating voltage AC (UL-listed)   | 30 V |
| Operating voltage DC (UL-listed)   | 30 V |
| Current operating per contact max. | 4 A  |

Installation | Connection

|                           |         |
|---------------------------|---------|
| Stripping length (jacket) | 20 mm   |
| Mounting set              | M12 x 1 |

Device protection | Electrical

|                                        |                   |
|----------------------------------------|-------------------|
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 1,5 kV            |
| Material group (IEC 60664-1)           | I                 |

Mechanical data | Material data

|                           |                  |
|---------------------------|------------------|
| Coating locking           | Nickeled         |
| Coating of fitting        | nickel plated    |
| Locking material          | Zinc die-casting |
| Material screw connection | Zinc die-casting |

Mechanical data | Mounting data

|                 |                                       |
|-----------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
|-----------------|---------------------------------------|

Environmental characteristics | Climatic

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

Conformity

|                  |                          |
|------------------|--------------------------|
| Product standard | DIN EN 61076-2-101 (M12) |
|------------------|--------------------------|

| Installation   Cable                                    |                                                                |
|---------------------------------------------------------|----------------------------------------------------------------|
| Cable identification                                    | 841                                                            |
| Jacket Color                                            | violet                                                         |
| Type of Certificate                                     | cURus                                                          |
| Amount stranding                                        | 1                                                              |
| Stranding                                               | 2 wires with 2 Filler twisted                                  |
| Cable shielding (type)                                  | copper braid, tinned                                           |
| Cable shielding (coverage)                              | 85 %                                                           |
| Banding                                                 | Fleece, Foil                                                   |
| Filler                                                  | yes                                                            |
| wire arrangement                                        | red, green                                                     |
| No. of bending cycles (C-track)                         | 5 Mio. @ 25 °C                                                 |
| Cable weight                                            | 70,4 g/m                                                       |
| Material jacket                                         | PUR                                                            |
| Shore hardness jacket                                   | 87 ± 3 Shore A                                                 |
| Freedom from ingredients (jacket)                       | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Outer-diameter (jacket)                                 | 7,7 mm                                                         |
| Tolerance outer diameter (sheath)                       | ± 5 %                                                          |
| Amount wires                                            | 2                                                              |
| Outer diameter insulation                               | 2,55 mm                                                        |
| Outer diameter tolerance core insulation                | ± 5 %                                                          |
| Shore hardness wire insulation                          | 60 ± 3 Shore D                                                 |
| Ingredient freeness wire insulation                     | lead-free, cadmium-free, CFC-free, halogen-free                |
| Amount strands (wire)                                   | 19                                                             |
| Diameter of single wires                                | 24 AWG                                                         |
| Conductor crosssection (wire)                           | 24 AWG                                                         |
| Material conductor wire                                 | Stranded copper wire, bare                                     |
| Traversing distance (C-track)                           | 5 m @ 25 °C   horizontal                                       |
| Current load capacity (standard)                        | to DIN VDE 0298-4                                              |
| Current load capacity min. wire                         | 4,5 A                                                          |
| Electrical resistance line constant wire                | 72,2 Ω/km @ 20 °C                                              |
| Nominal voltage power AC max.                           | 300 V                                                          |
| Electric capacitance (power)                            | 29000 pF/km                                                    |
| AC withstand voltage power (wire - shield)              | 2 kV @ 60 s                                                    |
| Power frequency withstand voltage power (wire - jacket) | 2 kV @ 60 s                                                    |
| AC withstand voltage power (wire - wire)                | 2 kV @ 60 s                                                    |
| Min. operating temperature (static)                     | -40 °C                                                         |
| Max. operating temperature (fixed)                      | 80 °C                                                          |
| Operating temperature min. (dynamic)                    | -20 °C                                                         |
| Operating temperature max. (dynamic)                    | 70 °C                                                          |
| Flame resistance                                        | IEC 60332-2-2   UL 1581 § 1100 FT2   UL 1581 § 1090            |
| chemical resistance                                     | Good, application-related testing                              |
| Gasoline resistance                                     | Good, application-related testing                              |
| Oil resistance                                          | Good, application-related testing   DIN EN 60811-404           |
| Bending radius (fixed)                                  | 7,5 x Outer diameter                                           |
| Bending radius (dynamic)                                | 12 x Outer diameter                                            |