

M12 male 0° A-cod. / MSUD valve plug A-18mm

PUR 5x0.34 ye UL/CSA+robot+drag ch. 2m

MSUD

Form A (18 mm) – M12, male straight

24 V DC $\pm 25\%$




LED (yellow/green)

for pressure switches

Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**



Product may differ from Image



Cable length	2 m
Side 1	
Tightening torque	0,4 Nm
Family construction form	MSUD
Thread	M3
Material	PUR
Degree of protection (EN IEC 60529)	IP67
Side 2	
Tightening torque	0,6 Nm
Family construction form	M12
Thread	M12 x 1
suitable for corrugated tube (internal Ø)	10 mm
Material	PBT
Width across flats	SW13
Degree of protection (EN IEC 60529)	IP67
取引条件	
ECLASS-6.0	27279218
ECLASS-7.0	27279218
ECLASS-8.0	27279218
ECLASS-9.0	27060311
ECLASS-10.1	27060312
ECLASS-11.1	27060312
ECLASS-12.0	27060312
ETIM-5.0	EC001855
GTIN	4048879447805
HSコード	85444290
Packaging unit	1
Electrical data Supply	
Operating voltage DC	24 V
Operating voltage DC min.	18 V
Operating voltage DC max.	30 V
Current operating per contact max.	4 A

Current consumption max.15 mA

Diagnostics

Status indication LEDgreen, yellow

Device protection | Electrical

Additional condition protection degreeinserted, screwed

Pollution Degree3

Rated surge voltage0,8 kV

Material group (IEC 60664-1)I

Mechanical data | Material data

Coating lockingsafe-cover coated

Color housingblack

Material gasketPUR

Material housingPlastic

Locking materialZinc die-casting

Mechanical data | Mounting data

Mounting methodinserted, screwed

Environmental characteristics | Climatic

Operating temperature min.-25 °C

Operating temperature max.85 °C

Additional condition temperature rangedepending on cable quality

Important installation notes

Note on strain reliefProtect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Note on bending radius**Attention:** Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.

Installation | Cable

wire arrangementbrown, black, blue, white, green-yellow

Cable identification055

Cable Type5

Jacket Coloryellow

Type of CertificatecURus

Amount stranding1

Stranding5 wires around Core filler twisted

Filleryes

wire arrangementbrown, black, blue, white, green-yellow

Cable weigth41,8 g/m

Material jacketPUR

Shore hardness jacket58 ± 3 Shore D

Freedom from ingredients (jacket)lead-free, cadmium-free, CFC-free, halogen-free, silicone-free

Outer-diameter (jacket)5 mm

Tolerance outer diameter (sheath)± 5 %

Material wire insulationPP

Amount wires5

Outer diameter insulation1,25 mm

Outer diameter tolerance core insulation± 5 %

Shore hardness wire insulation74 ± 3 Shore D

Ingredient freeness wire insulationlead-free, cadmium-free, CFC-free, halogen-free, silicone-free

Amount strands (wire)42

Diameter of single wires0,1 mm

Conductor crossection (wire)0,34 mm²

Material conductor wireStranded copper wire, bare

Conductor type (wire)strand class 6

Nominal voltage AC max.300 V

Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity min. wire	4,5 A
Electrical resistance line constant wire	60 Ω/km @ 20 °C
AC withstand voltage (wire - wire)	2,5 kV @ 60 s
Power frequency withstand voltage (wire - jacket)	2,5 kV @ 60 s
Min. operating temperature (static)	-40 °C
Max. operating temperature (fixed)	80 °C / 90 °C @ 10000 h Operation
Operating temperature min. (dynamic)	-25 °C
Operating temperature max. (dynamic)	80 °C / 90 °C @ 10000 h Operation
Flame resistance	UL 1581 § 1090 IEC 60332-2-2 UL 1581 § 1100 FT2
chemical resistance	Good, application-related testing
Gasoline resistance	Good, application-related testing
Oil resistance	DIN EN 60811-404 Good, application-related testing
Bending radius (fixed)	5 x Outer diameter
Bending radius (dynamic)	10 x Outer diameter
No. of bending cycles (C-track)	10 Mio. @ 25 °C
Traversing distance (C-track)	5 m @ 25 °C horizontal
Travel speed (C-track)	3,3 m/s @ 25 °C
No. of torsion cycles	1 Mio.
Torsion stress	± 360 °/m
Torsion speed	35 cycles/min