

**M12 male 90° / M8 female 0° A-cod.**

PUR 3x0.25 ye UL/CSA+drag ch. 0.6m

Male 90° – female straight

M12 – M8, 3-pole

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

[Link to Product](#)**Illustration**

|   |    |   |
|---|----|---|
| 1 | BN | 1 |
|   |    | 2 |
| 3 | BU | 3 |
| 4 | BK | 4 |





Product may differ from Image



|                                     |                   |
|-------------------------------------|-------------------|
| Cable length                        | 0,6 m             |
| Side 1                              |                   |
| Tightening torque                   | 0,6 Nm            |
| Mounting method                     | inserted, screwed |
| Family construction form            | M12               |
| Thread                              | M12 x 1           |
| Material                            | PUR               |
| Width across flats                  | SW13              |
| Degree of protection (EN IEC 60529) | IP66K, IP67       |
| Side 2                              |                   |
| Tightening torque                   | 0,4 Nm            |
| Mounting method                     | inserted, screwed |
| Family construction form            | M8                |
| Thread                              | M8 x 1            |
| Material                            | PUR               |
| Width across flats                  | SW9               |
| Degree of protection (EN IEC 60529) | IP66K, IP67       |
| 取引条件                                |                   |
| ECLASS-6.0                          | 27279218          |
| ECLASS-7.0                          | 27279218          |
| ECLASS-8.0                          | 27279218          |
| ECLASS-9.0                          | 27060311          |
| ECLASS-10.1                         | 27060311          |
| ECLASS-11.1                         | 27060311          |
| ECLASS-12.0                         | 27060311          |
| ETIM-5.0                            | EC001855          |
| GTIN                                | 4048879159029     |
| HSコード                               | 85444290          |
| Packaging unit                      | 1                 |
| Electrical data   Supply            |                   |
| Operating voltage AC max.           | 250 V             |
| Operating voltage DC max.           | 250 V             |

Current operating per contact max. 4 A

Device protection | Electrical

|                                        |                   |
|----------------------------------------|-------------------|
| Additional condition protection degree | inserted, screwed |
| Rated surge voltage                    | 1,5 kV            |

Mechanical data | Material data

|                           |                  |
|---------------------------|------------------|
| Coating of fitting        | nickel plated    |
| Material screw connection | Zinc die-casting |

Mechanical data | Mounting data

|                 |                                       |
|-----------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
|-----------------|---------------------------------------|

Environmental characteristics | Climatic

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

Important installation notes

|                        |                                                                                                                                                       |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on strain relief  | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |

Installation | Cable

|                                                   |                                                                |
|---------------------------------------------------|----------------------------------------------------------------|
| Cable identification                              | 030                                                            |
| Cable Type                                        | 3                                                              |
| Jacket Color                                      | yellow                                                         |
| Type of Certificate                               | cURus                                                          |
| Amount stranding                                  | 1                                                              |
| Stranding                                         | 3 wires twisted                                                |
| wire arrangement                                  | brown, black, blue                                             |
| Cable weigth                                      | 26,4 g/m                                                       |
| Material jacket                                   | PUR                                                            |
| Shore hardness jacket                             | 90 ± 5 Shore A                                                 |
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Outer-diameter (jacket)                           | 4,1 mm                                                         |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                          |
| Material wire insulation                          | PP                                                             |
| Amount wires                                      | 3                                                              |
| Outer diameter insulation                         | 1,25 mm                                                        |
| Outer diameter tolerance core insulation          | ± 5 %                                                          |
| Shore hardness wire insulation                    | 70 ± 5 Shore D                                                 |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Amount strands (wire)                             | 32                                                             |
| Diameter of single wires                          | 0,1 mm                                                         |
| Conductor crossection (wire)                      | 0,25 mm²                                                       |
| Material conductor wire                           | Stranded copper wire, bare                                     |
| Conductor type (wire)                             | strand class 6                                                 |
| Traversing distance (C-track)                     | 10 m @ 25 °C   horizontal                                      |
| Nominal voltage AC max.                           | 300 V                                                          |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                              |
| Current load capacity min. wire                   | 4,5 A                                                          |
| Electrical resistance line constant wire          | 79 Ω/km @ 20 °C                                                |
| AC withstand voltage (wire - wire)                | 2,5 kV @ 60 s                                                  |
| Power frequency withstand voltage (wire - jacket) | 2,5 kV @ 60 s                                                  |
| Min. operating temperature (static)               | -40 °C                                                         |
| Max. operating temperature (fixed)                | 80 °C / 90 °C @ 10000 h Operation                              |

|                                      |                                                      |
|--------------------------------------|------------------------------------------------------|
| Operating temperature min. (dynamic) | -25 °C                                               |
| Operating temperature max. (dynamic) | 80 °C / 90 °C @ 10000 h Operation                    |
| Flame resistance                     | IEC 60332-2-2   UL 1581 § 1100 FT2   UL 1581 § 1090  |
| chemical resistance                  | Good, application-related testing                    |
| Gasoline resistance                  | Good, application-related testing                    |
| Oil resistance                       | Good, application-related testing   DIN EN 60811-404 |
| Bending radius (fixed)               | 5 x Outer diameter                                   |
| Bending radius (dynamic)             | 10 x Outer diameter                                  |
| Travel speed (C-track)               | 10 Mio. @ 25 °C                                      |
| No. of torsion cycles                | 2 Mio.                                               |
| Torsion stress                       | ± 180 °/m                                            |
| Torsion speed                        | 35 cycles/min                                        |