



RJ45 male 45° up with cable shielded

PVC 1x4xAWG22 shielded gn UL/CSA+drag ch. 1.5m


Ethernet CAT5e  
Male 45° on top  
RJ45, 4-pole  
shielded  
Further cable lengths on request.  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image



Cable length 1,5 m

取引条件

ECLASS-6.0 27061801

|                |               |
|----------------|---------------|
| ECLASS-6.1     | 27060307      |
| ECLASS-7.0     | 27060307      |
| ECLASS-8.0     | 27060307      |
| ECLASS-9.0     | 27060307      |
| ECLASS-10.1    | 27060307      |
| ECLASS-11.1    | 27060307      |
| ECLASS-12.0    | 27060307      |
| ETIM-5.0       | EC002599      |
| GTIN           | 4048879547949 |
| HSコード          | 85444210      |
| Packaging unit | 1             |

Electrical data | Supply

|                                       |       |
|---------------------------------------|-------|
| Operating voltage DC max.             | 60 V  |
| Operating voltage DC max. (UL-listed) | 30 V  |
| Current operating per contact max.    | 1,5 A |

Industrial communication

|                             |                                                  |
|-----------------------------|--------------------------------------------------|
| Transfer parameters         | CAT5, Class D (ISO/IEC 11801:2002), (EN 50173-1) |
| Data transmission rate max. | 100 MBit/s                                       |

Industrial communication | Ethernet functionality

|        |             |
|--------|-------------|
| duplex | Full duplex |
|--------|-------------|

Device protection | Electrical

|                                        |                   |
|----------------------------------------|-------------------|
| Degree of protection (EN IEC 60529)    | IP20              |
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 1 kV              |
| Material group (IEC 60664-1)           | I                 |

Mechanical data

|                             |         |
|-----------------------------|---------|
| Contour for corrugated hose | without |
|-----------------------------|---------|

Mechanical data | Material data

|                  |     |
|------------------|-----|
| Material housing | PUR |
| Locking material | PA  |

Environmental characteristics | Climatic

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

Important installation notes

|                        |                                                                                                                                                       |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on strain relief  | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |

Installation | Cable

|                            |                                           |
|----------------------------|-------------------------------------------|
| Cable identification       | 800                                       |
| Jacket Color               | green                                     |
| Type of Certificate        | cURus                                     |
| Amount stranding           | 1                                         |
| Stranding                  | 4 wires around Filler star-shaped twisted |
| Cable shielding (type)     | copper braid, tinned                      |
| Cable shielding (coverage) | 85 %                                      |
| Banding                    | Foil                                      |
| Filler                     | yes                                       |
| wire arrangement           | yellow, blue, orange, white               |
| Cable weighth              | 73,7 g/m                                  |

|                                                   |                                                      |
|---------------------------------------------------|------------------------------------------------------|
| Material jacket                                   | PVC                                                  |
| Shore hardness jacket                             | 85 ± 5 Shore A                                       |
| Freedom from ingredients (jacket)                 | lead-free, CFC-free                                  |
| Outer-diameter (jacket)                           | 6,6 mm                                               |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                |
| Material inner jacket                             | FRNC                                                 |
| Color (inner jacket)                              | natur                                                |
| Material wire insulation                          | PE                                                   |
| Amount wires                                      | 4                                                    |
| Outer diameter insulation                         | 1,53 mm                                              |
| Outer diameter tolerance core insulation          | ± 5 %                                                |
| Shore hardness wire insulation                    | 55 ± 5 Shore D                                       |
| Ingredient freeness wire insulation               | lead-free, CFC-free, halogen-free                    |
| Amount strands (wire)                             | 7                                                    |
| Diameter of single wires                          | 22 AWG                                               |
| Conductor crossection (wire)                      | 22 AWG                                               |
| Material conductor wire                           | Stranded copper wire, bare                           |
| Traversing distance (C-track)                     | 5 m @ 25 °C                                          |
| Nominal voltage AC max.                           | 300 V                                                |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                   | 4,8 A                                                |
| Characteristic impedance                          | 100 Ω ± 15 % @ 1 MHz                                 |
| Electrical resistance line constant wire          | 55 Ω/km @ 20 °C                                      |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                          |
| Electrical capacity line constant (wire - wire)   | 50000 pF/km                                          |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                          |
| AC withstand voltage (wire - shield)              | 2 kV @ 60 s                                          |
| Min. operating temperature (static)               | -30 °C                                               |
| Max. operating temperature (fixed)                | 80 °C                                                |
| Operating temperature min. (dynamic)              | -10 °C                                               |
| Operating temperature max. (dynamic)              | 70 °C                                                |
| Flame resistance                                  | UL 1581 § 1090   UL 1581 § 1100 FT2   IEC 60332-2-2  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404 |
| Bending radius (fixed)                            | 5 x Outer diameter                                   |
| Bending radius (dynamic)                          | 15 x Outer diameter                                  |
| Travel speed (C-track)                            | 2 Mio. @ 25 °C                                       |