

M12 female 0° A-cod. with cable Lite




PUR 4x0.34 gy UL/CSA 5m

**⚠ NOTICE ⚠**  
**PRODUCT IS DISCONTINUED. PLEASE HAVE A LOOK AT THE ALTERNATIVE PRODUCTS.**

Female straight  
M12, 4-pole  
7005 - plastic hexagonal screw (M12 Lite)  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.  
Further cable lengths on request.

[Link to Product](#)

Illustration



Product may differ from Image



Cable length 5 m

| Side 1                                    |                                                                                                                                                       |
|-------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Tightening torque                         | 0,6 Nm                                                                                                                                                |
| Family construction form                  | M12                                                                                                                                                   |
| Thread                                    | M12 x 1                                                                                                                                               |
| suitable for corrugated tube (internal Ø) | 10 mm                                                                                                                                                 |
| Coding                                    | A                                                                                                                                                     |
| Width across flats                        | SW13                                                                                                                                                  |
| Degree of protection (EN IEC 60529)       | IP65, IP66K, IP67                                                                                                                                     |
| 取引条件                                      |                                                                                                                                                       |
| ECLASS-6.0                                | 27279218                                                                                                                                              |
| ECLASS-6.1                                | 27279218                                                                                                                                              |
| ECLASS-7.0                                | 27279218                                                                                                                                              |
| ECLASS-8.0                                | 27279218                                                                                                                                              |
| ECLASS-9.0                                | 27060311                                                                                                                                              |
| ECLASS-10.1                               | 27060311                                                                                                                                              |
| ECLASS-11.1                               | 27060311                                                                                                                                              |
| ECLASS-12.0                               | 27060311                                                                                                                                              |
| ETIM-5.0                                  | EC001855                                                                                                                                              |
| GTIN                                      | 4048879407731                                                                                                                                         |
| HSコード                                     | 85444290                                                                                                                                              |
| Packaging unit                            | 1                                                                                                                                                     |
| Electrical data   Supply                  |                                                                                                                                                       |
| Operating voltage AC max.                 | 250 V                                                                                                                                                 |
| Operating voltage DC max.                 | 250 V                                                                                                                                                 |
| Operating voltage AC (UL-listed)          | 30 V                                                                                                                                                  |
| Operating voltage DC (UL-listed)          | 30 V                                                                                                                                                  |
| Current operating per contact max.        | 4 A                                                                                                                                                   |
| Device protection   Electrical            |                                                                                                                                                       |
| Pollution Degree                          | 3                                                                                                                                                     |
| Rated surge voltage                       | 2,5 kV                                                                                                                                                |
| Material group (IEC 60664-1)              | I                                                                                                                                                     |
| Mechanical data   Material data           |                                                                                                                                                       |
| Material housing                          | PUR                                                                                                                                                   |
| Locking material                          | PA                                                                                                                                                    |
| Mechanical data   Mounting data           |                                                                                                                                                       |
| Mounting method                           | inserted, screwed, Shaking protection                                                                                                                 |
| Environmental characteristics   Climatic  |                                                                                                                                                       |
| Operating temperature min.                | -25 °C                                                                                                                                                |
| Operating temperature max.                | 85 °C                                                                                                                                                 |
| Additional condition temperature range    | depending on cable quality                                                                                                                            |
| Important installation notes              |                                                                                                                                                       |
| Note on strain relief                     | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius                    | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |
| Conformity                                |                                                                                                                                                       |
| Product standard                          | DIN EN 61076-2-101 (M12)                                                                                                                              |
| Cable                                     |                                                                                                                                                       |
| Cable identification                      | 224                                                                                                                                                   |
| Cable Type                                | 2 (PUR/PVC)                                                                                                                                           |
| Approval (cable)                          | UL (AWM-Style 20549/1731), CSA; CE conform                                                                                                            |
| Cable weight [g/m]                        | 42,68 g                                                                                                                                               |

|                                   |                                                                                                                                                        |
|-----------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| Material wire                     | Cu wire, bare                                                                                                                                          |
| Resistor (core)                   | max. 57 $\Omega$ /km (20 °C)                                                                                                                           |
| Single wire Ø (core)              | 0.1 mm                                                                                                                                                 |
| Construction (core)               | 42× 0.1 mm (multi-strand wire class 6)                                                                                                                 |
| Diameter (core)                   | 4× 0.34 mm <sup>2</sup>                                                                                                                                |
| AWG                               | similar to AWG 22                                                                                                                                      |
| Material wire isolation           | PVC                                                                                                                                                    |
| Material property wire insulation | CFC-, cadmium-, silicone- and lead-free                                                                                                                |
| Shore hardness wire isolation     | 43 ±5 D                                                                                                                                                |
| Wire-Ø incl. isolation            | 1.25 mm ±5%                                                                                                                                            |
| Color/numbering of wires          | br, bk, bl, wh                                                                                                                                         |
| Stranding combination             | 4 wires twisted                                                                                                                                        |
| Shield                            | no                                                                                                                                                     |
| Material jacket                   | PUR/PVC                                                                                                                                                |
| Material property (jacket)        | CFC-, halogen-, cadmium-, silicone- and lead-free, matt, low-adhesion, machine easy to process, abrasion-resistant, hydrolysis and microbial resistant |
| Shore hardness jacket             | 80 ±5 A (PVC-under jacket); 85 ±5 A (PUR-jacket)                                                                                                       |
| Outer-Ø (jacket)                  | 4.6 mm ±5%                                                                                                                                             |
| Color jacket                      | gray                                                                                                                                                   |
| chemical resistance               | good resistance to oil, gasoline and chemicals                                                                                                         |
| Nominal voltage                   | UL 300 V AC                                                                                                                                            |
| Test voltage                      | 2000 V AC                                                                                                                                              |
| Current load capacity             | to DIN VDE 0298-4                                                                                                                                      |
| Temperature range (fixed)         | -30...+80 °C                                                                                                                                           |
| Temperature range (mobile)        | -5...+80 °C                                                                                                                                            |
| Bending radius (fixed)            | 10× outer Ø                                                                                                                                            |
| Bending radius (dynamic)          | 15× outer Ø                                                                                                                                            |
| No. of bending cycles (C-track)   | max. 2 Mio. (25 °C)                                                                                                                                    |
| Travel speed (C-track)            | max. 3.3 m/s                                                                                                                                           |
| Acceleration (C-track)            | max. 5 m/s <sup>2</sup>                                                                                                                                |