


Cable drum Ø 355mm

PVC 3x0.75 gy 100m

Cable drum (100 m)  
PVC  
3× 0.75 mm², grey

Link to Product

Illustration



Product may differ from Image

| 取引条件                              |                                                  |
|-----------------------------------|--------------------------------------------------|
| ECLASS-6.0                        | 27062011                                         |
| ECLASS-6.1                        | 27061801                                         |
| ECLASS-7.0                        | 27061801                                         |
| ECLASS-8.0                        | 27061801                                         |
| ECLASS-9.0                        | 27061801                                         |
| ECLASS-10.1                       | 27061801                                         |
| ECLASS-11.1                       | 27061801                                         |
| ECLASS-12.0                       | 27061801                                         |
| ETIM-5.0                          | EC001855                                         |
| GTIN                              | 4048879340427                                    |
| HSコード                             | 85444995                                         |
| Packaging unit                    | 1                                                |
| Installation   Cable              |                                                  |
| Cable identification              | 216                                              |
| Cable Type                        | 1                                                |
| Printing color of wire insulation | white (isolation black)                          |
| Jacket Color                      | gray                                             |
| Amount stranding                  | 1                                                |
| Stranding                         | 3 wires twisted                                  |
| wire arrangement                  | black 1, black 2, green-yellow                   |
| Cable weigth                      | 63,8 g/m                                         |
| Material jacket                   | PVC                                              |
| Shore hardness jacket             | 80 ± 5 Shore A                                   |
| Freedom from ingredients (jacket) | lead-free, cadmium-free, CFC-free, silicone-free |
| Outer-diameter (jacket)           | 5,9 mm                                           |
| Tolerance outer diameter (sheath) | ± 5 %                                            |

|                                                   |                                                      |
|---------------------------------------------------|------------------------------------------------------|
| Material wire insulation                          | PVC                                                  |
| Amount wires                                      | 3                                                    |
| Outer diameter insulation                         | 1,8 mm                                               |
| Outer diameter tolerance core insulation          | ± 5 %                                                |
| Shore hardness wire insulation                    | 43 ± 5 Shore D                                       |
| Material properties wire insulation               | good machinability                                   |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, silicone-free     |
| Printing color of wire insulation                 | white (isolation black)                              |
| Amount strands (wire)                             | 24                                                   |
| Diameter of single wires                          | 0,2 mm                                               |
| Conductor crosssection (wire)                     | 0,75 mm²                                             |
| Material conductor wire                           | Stranded copper wire, bare                           |
| Conductor type (wire)                             | Strand class 5                                       |
| Max. rated voltage (conductor - conductor)        | 500 V                                                |
| Max. rated voltage (conductor - ground)           | 300 V                                                |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                   | 12 A                                                 |
| Electrical resistance line constant wire          | 26 Ω/km @ 20 °C                                      |
| AC withstand voltage (wire - wire)                | 3 kV @ 60 s                                          |
| Power frequency withstand voltage (wire - jacket) | 3 kV @ 60 s                                          |
| Min. operating temperature (static)               | -30 °C                                               |
| Max. operating temperature (fixed)                | 70 °C                                                |
| Operating temperature min. (dynamic)              | -5 °C                                                |
| Operating temperature max. (dynamic)              | 70 °C                                                |
| Flame resistance                                  | UL 1581 § 1090   IEC 60332-2-2   UL 1581 § 1100 FT2  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404 |
| Bending radius (fixed)                            | 5 x Outer diameter                                   |
| Bending radius (dynamic)                          | 10 x Outer diameter                                  |