



MQ15-X-Power female 0° with cable

PUR 4x2.5 bk UL/CSA+drag chain 15m

Female straight  
MQ15, 4-pole  
without cable sleeves  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.  
Further cable lengths on request.

Link to Product

Illustration



Product may differ from Image

|              |      |
|--------------|------|
| Cable length | 15 m |
|--------------|------|

| Side 1                   |                   |
|--------------------------|-------------------|
| Mounting method          | inserted, screwed |
| Coating contact          | silver-plated     |
| Family construction form | MQ15              |
| Material contact         | Copper alloy      |
| No. of poles             | 4                 |
| Side 2                   |                   |

Stripping length (jacket)30 mm

| 取引条件           |               |
|----------------|---------------|
| ECLASS-6.0     | 27279218      |
| ECLASS-6.1     | 27279218      |
| ECLASS-7.0     | 27279218      |
| ECLASS-8.0     | 27279218      |
| ECLASS-9.0     | 27060327      |
| ECLASS-10.1    | 27060311      |
| ECLASS-11.1    | 27060311      |
| ECLASS-12.0    | 27060327      |
| ETIM-5.0       | EC001855      |
| GTIN           | 4048879660877 |
| HSコード          | 85444290      |
| Packaging unit | 1             |

| Electrical data   Supply           |       |
|------------------------------------|-------|
| Operating voltage AC max.          | 600 V |
| Current operating per contact max. | 16 A  |

| Diagnostics           |    |
|-----------------------|----|
| Status indication LED | no |

| Installation   Connection |       |
|---------------------------|-------|
| Stripping length (jacket) | 30 mm |
| Mating cycles min.        | 500   |

| Installation   Pin assignment |            |
|-------------------------------|------------|
| Configuration                 | fully used |

| Device protection   Electrical         |                   |
|----------------------------------------|-------------------|
| Degree of protection (EN IEC 60529)    | IP67              |
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 4 kV              |
| Material group (IEC 60664-1)           | I                 |

| Mechanical data   Material data     |         |
|-------------------------------------|---------|
| Combustibility class housing (UL94) | HB      |
| Material housing                    | Plastic |
| Material contact carrier            | PA      |

| Mechanical data   Mounting data |                 |
|---------------------------------|-----------------|
| Looking techniques              | bayonet-locking |

| Environmental characteristics   Climatic |                            |
|------------------------------------------|----------------------------|
| Operating temperature min.               | -25 °C                     |
| Operating temperature max.               | 80 °C                      |
| Additional condition temperature range   | depending on cable quality |

| Installation   Cable              |                                         |
|-----------------------------------|-----------------------------------------|
| Cable identification              | P03                                     |
| Jacket Color                      | black                                   |
| wire arrangement                  | black 1, black 2, black 3, green-yellow |
| Material jacket                   | PUR                                     |
| Freedom from ingredients (jacket) | halogen-free, LABS-free                 |
| Outer-diameter (jacket)           | 9 mm                                    |
| Tolerance outer diameter (sheath) | ± 5 %                                   |
| Material wire insulation          | TPE                                     |
| Amount wires                      | 4                                       |

|                                                   |                                                      |
|---------------------------------------------------|------------------------------------------------------|
| Ingredient freeness wire insulation               | halogen-free, LABS-free                              |
| Conductor crossection (wire)                      | 2,5 mm²                                              |
| Material conductor wire                           | Stranded copper wire, bare                           |
| Nominal voltage AC max.                           | 1000 V                                               |
| Electrical resistance line constant wire          | 8 Ω/km @ 20 °C                                       |
| AC withstand voltage (wire - wire)                | 4 kV                                                 |
| Power frequency withstand voltage (wire - jacket) | 4 kV                                                 |
| Min. operating temperature (static)               | -50 °C                                               |
| Max. operating temperature (fixed)                | 80 °C                                                |
| Operating temperature min. (dynamic)              | -20 °C                                               |
| Operating temperature max. (dynamic)              | 70 °C                                                |
| Flame resistance                                  | IEC 60332-2-2   UL 1581 § 1090   UL 1581 § 1100 FT2  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | DIN EN 60811-404   Good, application-related testing |
| Bending radius (fixed)                            | 4 x Outer diameter                                   |
| Bending radius (dynamic)                          | 10 x Outer diameter                                  |
| Travel speed (C-track)                            | 5 Mio.                                               |
| Torsion stress                                    | ± 15 °/m                                             |