



PRE-WIRED CAP FOR EXACT8, 6XM8, 4 POLE

5.0m PUR 12x0.34+2x0,75, UL/CSA

5.0 m

[Link to Product](#)

Illustration



Product may differ from Image



| 取引条件        |          |
|-------------|----------|
| ECLASS-6.0  | 27143423 |
| ECLASS-6.1  | 27279219 |
| ECLASS-7.0  | 27279219 |
| ECLASS-8.0  | 27279219 |
| ECLASS-9.0  | 27440108 |
| ECLASS-10.1 | 27440108 |
| ECLASS-11.1 | 27440108 |
| ECLASS-12.0 | 27440108 |

|                                                 |                                                                                                                                 |
|-------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| ETIM-5.0                                        | EC002585                                                                                                                        |
| GTIN                                            | 4048879054836                                                                                                                   |
| HSコード                                           | 85444290                                                                                                                        |
| Packaging unit                                  | 1                                                                                                                               |
| Electrical data   Supply                        |                                                                                                                                 |
| Total current max.                              | 8 A                                                                                                                             |
| Device protection   Media                       |                                                                                                                                 |
| Flame resistance                                | flame retardant                                                                                                                 |
| Mechanical data   Material data                 |                                                                                                                                 |
| Material housing                                | Plastic                                                                                                                         |
| Environmental characteristics   Climatic        |                                                                                                                                 |
| Operating temperature min.                      | -20 °C                                                                                                                          |
| Operating temperature max.                      | 80 °C                                                                                                                           |
| Additional condition temperature range          | depending on cable quality                                                                                                      |
| Installation   Cable                            |                                                                                                                                 |
| Cable identification                            | 389                                                                                                                             |
| Jacket Color                                    | gray                                                                                                                            |
| Type of Certificate                             | cURus, CSA                                                                                                                      |
| Amount stranding                                | 1                                                                                                                               |
| Stranding                                       | 4 wires twisted                                                                                                                 |
| Amount stranding (type 2)                       | 1                                                                                                                               |
| Stranding (type 2)                              | 10 wires around Stranding combination twisted                                                                                   |
| Banding                                         | Fleece                                                                                                                          |
| wire arrangement                                | red, yellow-white, gray-pink, pink, (brown, blue, brown-yellow, brown-green, green-white, red-blue, gray, yellow, green, white) |
| Cable weigth                                    | 122,1 g/m                                                                                                                       |
| Material jacket                                 | PUR                                                                                                                             |
| Shore hardness jacket                           | 89 ± 5 Shore A                                                                                                                  |
| Freedom from ingredients (jacket)               | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free, LABS-free                                                       |
| Outer-diameter (jacket)                         | 9,5 mm                                                                                                                          |
| Tolerance outer diameter (sheath)               | ± 5 %                                                                                                                           |
| Material wire insulation                        | TPE-E                                                                                                                           |
| Amount wires                                    | 10                                                                                                                              |
| Outer diameter insulation                       | 1,5 mm                                                                                                                          |
| Outer diameter tolerance core insulation        | ± 5 %                                                                                                                           |
| Shore hardness wire insulation                  | 55 ± 5 Shore D                                                                                                                  |
| Ingredient freeness wire insulation             | lead-free, cadmium-free, CFC-free, halogen-free                                                                                 |
| Traversing distance (C-track)                   | 5 m @ 25 °C   horizontal                                                                                                        |
| Amount strands (wire)                           | 42                                                                                                                              |
| Diameter of single wires                        | 0,1 mm                                                                                                                          |
| Conductor crosssection (wire)                   | 0,34 mm²                                                                                                                        |
| Material conductor wire                         | Stranded copper wire, bare                                                                                                      |
| Conductor type (wire)                           | strand class 6                                                                                                                  |
| Material wire insulation (Data)                 | TPE-E                                                                                                                           |
| Outer diameter wire insulation (Data)           | 1,8 mm                                                                                                                          |
| Tolerance outer diameter wire insulation (data) | ± 5 %                                                                                                                           |
| Shore hardness wire insulation (Data)           | 55 ± 5 Shore D                                                                                                                  |
| Ingredient freeness wire insulation (Data)      | lead-free, cadmium-free, CFC-free, halogen-free                                                                                 |
| Amount wires (Data)                             | 2                                                                                                                               |
| Amount strands wire (Data)                      | 42                                                                                                                              |
| Diameter of single wires (Data)                 | 0,15 mm                                                                                                                         |

|                                                   |                                                      |
|---------------------------------------------------|------------------------------------------------------|
| Conductor crossection wire (Data)                 | 0,75 mm²                                             |
| Material conductor wire (Data)                    | Stranded copper wire, bare                           |
| Wire conductor type (Data)                        | strand class 6                                       |
| Max. rated voltage (conductor - conductor)        | 300 V                                                |
| Max. rated voltage (conductor - ground)           | 300 V                                                |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                   | 4 A                                                  |
| Current load capacity min. Wire (Data)            | 12 A                                                 |
| Electrical resistance line constant wire          | 57 Ω/km @ 20 °C                                      |
| Electrical resistance coating wire (Data)         | 26 Ω/km @ 20 °C                                      |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                          |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                          |
| Min. operating temperature (static)               | -40 °C                                               |
| Max. operating temperature (fixed)                | 80 °C                                                |
| Operating temperature min. (dynamic)              | -5 °C                                                |
| Operating temperature max. (dynamic)              | 80 °C                                                |
| Flame resistance                                  | UL 1581 § 1100 FT2   IEC 60332-2-2   UL 1581 § 1090  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404 |
| Bending radius (installation)                     | x Outer diameter                                     |
| Bending radius (fixed)                            | 7,5 x Outer diameter                                 |
| Bending radius (dynamic)                          | 10 x Outer diameter                                  |
| Travel speed (C-track)                            | 5 Mio. @ 25 °C                                       |

Connection type 3

|                          |                |
|--------------------------|----------------|
| Family construction form | free cable end |
| No. of poles             | 14             |
| Family construction form | free cable end |
| Color contact carrier    | gray           |
| No. of poles             | 18             |
| Family construction form | M8             |
| Gender                   | female         |
| Color contact carrier    | black          |
| Coding                   | A              |
| No. of poles             | 4              |
| PIN 1                    | +              |
| PIN 2                    | S 2            |
| PIN 3                    | -              |
| PIN 4                    | S 1            |