

Male module, 4-pole, crimp t.

830 V, 40 A


Male
4-pole
Crimp
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image



取引条件

ECLASS-6.0	27143424
ECLASS-6.1	27261204
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440217
ECLASS-10.1	27440217
ECLASS-11.1	27440217
ECLASS-12.0	27440217
ETIM-5.0	EC000438
GTIN	4048879641531
HSコード	85389099
Packaging unit	5

Electrical data | Supply

Operating voltage AC	830 V
Operating voltage DC	830 V
Operating current	40 A

Installation

Connection cross section min.	1,5 mm²
Connection cross section max.	6 mm²
AWG number min.	16
AWG number max.	10

Installation | Connection

Wire insulation diameter min.	5,2 mm
Connection	Crimp

Gender	male
Mating cycles min.	500
Installation Pin assignment	
No. of poles	4
Device protection Electrical	
Pollution Degree	3
Rated surge voltage	8 kV
Insulation resistance min.	100 MΩ
Overvoltage category (EN 60664-1)	I
Overvoltage category (EN 60950-1)	III
Mechanical data	
Holding force contacts min.	100 N
Holding force modules min.	240 N
Pulling force max.	220 N
Mechanical data Material data	
Coating contact	silver-plated
Combustibility class (UL94)	V-0
Material housing	PA
Material contact	Brass
Mechanical data Mounting data	
Number of module slots	1
Height	49,4 mm
Width	14,5 mm
Depth	34,4 mm
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	125 °C
Climatic category (EN IEC 60068-1)	40/125/10